

AUDIBAX

PP 4000

English

AUDIBAX Professional Mini Phono Preamp

1. UNPACKING AND INSPECTION

Carefully unpack your PP 4000 phono preamp. Do not discard any packing materials! If anything is missing or damaged, contact your dealer or Alctron immediately. Items included with the EQ73a are:

- PP 4000 Phono preamp
- Power adapter
- Set of instructions


The PP 4000 a phono preamp of exceptional sonic clarity and rugged construction. When used in accordance with the guidelines in this manual it will give you many years of outstanding performance.

2. GENERAL DESCRIPTION

The PP 4000 is a phono preamp which bring your record player's output up to proper line level, one pair of RCA inputs, and outputs on both RCA and stereo 1/4" connectors. Engineers know that optimizing the signal levels is the key to getting the most out of any sound system, PP 4000 help your record player play nicely with the rest of your gear.


- * Preamp Type: Solid State
- * Number of Channels: 1
- * Analog Inputs: 1 x stereo RCA
- * Analog Outputs: 1 x stereo RCA, 1 x 1/4"

3. TOP PANEL / FRONT



1. OUTPUT: 1/4" Tip-Ring-Sleeve jack for connection to a stereo amplifier,mixer or recording unit.
2. OUTPUT(L+R): Stereo RCA jacks for connection to a stereo amplifier,mixer or recording unit.
3. INPUT(L+R): Stereo RCA jacks for connection to the phono player.
4. POWER INPUT: 12 - 16 Volts DC, tip negative jack.
5. GROUND CONNECTOR: Connects to the Ground of the phono player.
6. ON/OFF SWITCH: Control the PP 4000 is working or not.

4. HARDWARE CONNECTIONS



5. SERVICE

If your PP 4000 Headphone needs servicing, follow these instructions.

- ☒ Ensure the problem is not related to operation error or external system devices.
- ☒ Keep this owner's manual. We don't need it to repair the unit.
- ☒ Pack the unit in its original packaging including end card and box. This is very important. If you have lost the packaging, please make sure you have packed the unit properly. AUDIBAX is not responsible for any damage that occurs due to non-factory packing.
- ☒ Ship to the AUDIBAX tech support center or the local return authorization.

AUDIBAX is constantly striving to maintain the highest professional standards. As a result of these efforts, modifications may be made from time to time to existing products without prior notice. Specifications and appearance may differ from those listed or illustrated.